



Rotary Cup Shrink Tunnel

Rotary cup shrink tunnel offers you the best solution for shrinking sleeves on bottles made of PET or other material. The radially adjustable rotating cups ensure that the bottles do not roll freely inside the chamber and provide uniform shrinkage of the sleeves.

Technical Data	QS2032STVROT
Voltage/Frequency (V/Hz)	415/50/3 Phase
Power (W)	8800
Conveyor Speed (m/min)	0-11
Maximum Loading (kg)	3
Shrink Film	POF, PVC
Machine Weight (kg)	143
Window Size (WxH) (mm)	200x320
Machine Dimensions (LxWxH) (mm)	2600x450x1180
Holder Dimensions (Dmin/Dmax) (mm)	40/120

PB#2, Kizhakkambalam PO, Kochi, Kerala, India-683562 Phone: +91 484 2680780 (100 Lines)

Sales: +91 8893 111 780 | +91 934 9030 780 | +91 9388 880 780, Email: mktg1@sevana.com | mktg@sevana.com